| Items | Technical Parameters | Remarks |
|---|---|---------|
| Dimensions | ARK-S2000-S: 2000 x 1990 x 1200 mm | |
| | ARK-S2000-M: 2600 x 2200 x 2100 mm | • |
| (W x H x D) | ARK-S2000-L: 5600 x 2200 x 2100 mm | |
| Value of Negative Pressure (Pa) | -25~-20 | • |
| Measurement Range of Pressure Gauge outside Cabin (Pa) | −30~+30 | • |
| Touch Screen outside Cabin (in) | 15.6 inches | • |
| Safety Delivery Window | Interlocking electric type + Ultraviolet disinfection (400×400mm) | • |
| Lighting System inside Cabin | Multi-scenario lighting mode | • |
| Air Change Times Per Hour | 30 | • |
| Disinfection inside Cabin | Mobile ultraviolet disinfection vehicle | • |
| | Intelligent ultraviolet disinfection facility | 0 |
| Intercom System | For communications of people inside the cabin with people outside the cabin | • |
| One-button Alarm | People inside the cabin can give an one-button alarm in case of emergency. | • |
| TV Entertainment System (inch) | ARK-S2000-S: 15; ARK-S2000-M/L: 32 | • |
| Fire extinguishers inside Cabin (Set) | 1 | • |
| Power Supply (V)/Frequency (Hz) | AC220/50 | • |
| Device Power (KW) | ≤ 0.8 | • |
| UPS Uninterruptible Power Supply | The power supply time after power off is equal or more than 3 hours. | • |
| Device Weight (kg) | ARK-S2000-S: ≤ 600 | |
| | ARK-S2000-M: ≤ 1000 | • |
| | ARK-S2000-L: ≤ 1800 | |
| Bottom Wheels | Adjustable universal wheels | • |
| Remote Video Monitoring System inside Cabin | Spherical camera | 0 |
| U-type Infusion Support on the Roof of Inside Cabin | Be used for patient infusion | 0 |
| Oxygen Supply Device inside Cabin | Oxygen terminal + power socket + Lamp + switch + beeper | 0 |
| Flushing-free Closestool inside Cabin | Single plastic packing type | 0 |
| Bed | Automobile medical bed | 0 |
| Note: ●Standard OOptional | | |